PTA pallet scales – versatile solutions for all industries

Application areas

- Goods receiving and shipping
- Manufacturing
- Packaging

Environments

- Wet or dry - Nonhazardous
- Hazardous categories 3G/D and
- 2G/D

Capacities

300 - 3000 kg

Certifiable resolution

Single range – multiple range – multi-interval

Interfaces

Analog – digital



You decide where you use it!

Are you looking for a scale to weigh pallets in a dry environment? The rugged, hot-dip galvanized pallet scale PTA455 with its scratch-resistant surface guarantees reliable service for many years.


Or are humidity, moisture, and corrosive easy-to-clean weighing platforms with high corrosion resistance? If so, the pallet scale PTA459/x made from stainless steel (1.4301 / AISI 304) will serve you well. Because the electronic components in the terminal box and the measuring cell have IP68 protection which makes them ideal for use in wet environments.

Everything depends on the resolution!

Single range – multi range – multiinterval?

Select the optimal resolution for your weighing process. All models which have a resolution of 1x3000e as standard are also available with the option of 1x6000e single range, 2x3000e multi range, 2x3000e multi liquids perhaps an issue? Are you looking for interval, or 3x3000e multi range. The stainless steel standard weighing platforms can be configured on-site with a certifiable multi range resolution of 2x3000e. For non-certifiable use, with the aid of the powerful A/D converter the pallet scale can be operated at a resolution of up to 30.000d (digits).

Weighing range 1 x 6000e SR 2 x 3000e MR/MI 3 x 3000e MR kg/kg kg/kg Range 1 Range 1 Range 2 Range 2 Range 3 300 0.05/300 0.05/150 0.1/300 600 0.1/600 0.1/300 0.05/150 0.2/600 0.1/300 0.2/600 1500 0.2/1200 0.2/600 0.5/1500 0.1/300 0.2/600 0.5/500 0.2/600 3000 0.5/3000 0.5/1500 1/3000 0.5/1500 1/3000



Use in hazardous areas

Is the location of your weighing solution classified according to explosion protection guidelines? We offer the optimal solution for zones 1/21 and 2/22.

You can use the standard version of the stainless steel pallet scale in the nonhazardous area as well as in zone 2/22 hazardous areas.

In combination with the intrinsically safe ID7sx display and power supply unit, the explosionproof versions of the stainless-steel pallet scales are the optimal weighing solution for zones 1 and 21. All these system components comply with the ATEX Directive 94/9/EC.

The hot-dip galvanized versions can only be used in nonhazardous areas.

Analog or digital weighing interfaces a question of philosophy

Minimize the installation time of your pallet scale, increase your flexibility, and utilize the benefits of digital (IDNet) weighing systems. Just plug in and start using. Up to 3 weighing platforms can be connected to a single terminal, as well as disconnected and reconnected as often as you like - even for legal applications!

Whether in nonhazardous or hazardous areas, the powerful A/D converter of the digital weighing platform guarantees precise and stable measurement values. The A/D converter has an amazing update rate of up to 20 / s as well as very fast stabilization.

Your weighing process determines your

choice of display unit. You can select from a wide range of display units with digital or analog interfaces to the scale. Besides simple weighing, the operating terminals can also be individually configured for your specific application:

- Available interfaces: CL, RS232, RS485, Ethernet, Profibus
- · Additional software modules for formula weighing, dispensing, totalization, counting, ...
- Peripheral devices such as printers, external keyboards, ...

Fully certified for the customer!

Save yourself additional costs for certification and installation with the fully certified weighing system.

We offer preferred models of hot-dip galvanized pallet scales with analog interface require from the following range: between the scale and a display unit – fully certified by the manufacturer, with all Internal width: 450 – 1000 mm country-specific settings!

Options and accessories – to meet your needs!

Are the standard length of 1260 mm and overall width of 600 mm not what you need? Then you can select the size you 500 – 1260 mm

Do you need a wider load-bearing surface? Stainless-steel models are available with a leg width of up to 275 mm.

If an additional leg width of 75 mm is already sufficient, the leg widener is a practical solution for both versions of the pallet scale.


If your requirements for corrosion resistance are not already met by the standard stainless-steel version (1.4301/AISI 304), you can choose a weighing platform of acid-resistant steel (AISI 316).

And do you need a smoother surface? On request, the stainless steel version is also available with a polished surface with roughness average Ra < 1 μm.

Customer-specific scales

Can you not find an appropriate solution for your specific application despite our comprehensive offerings? Then please contact us directly and we will tailor a solution for your individual case.









PTA455 with terminal IND425 - fully certified


	Leg width	Leg widener
PTA459(x) stainless	•	•
PTA455 hot-dip galvanized		•
The optional wheel set	gives y	ou greate


locational flexibility. With its low weight, the pallet scale can be moved to a different location without problem. For optimal handling, the front forks have built-in handgrips.


Moving the scale is even easier with the handle: just tilt the scale and roll it away. What's more, you can also mount the terminal on the handle.











Optional load plate PTA leg widener PTA wheel set PTA wheel set and handle

SR SingleRange, MR MultiRange, MI MultiInterval

Design and quality make the difference

A precision measuring instrument like a scale must deliver permanently exact measurement values even after many years of use in an industrial environment. The key to achieving this is the interplay of innovative technical design – tubular construction of the hot-dip galvanized model and bent/welded construction of the stainless steel model – with highquality materials and state-of-the-art manufacturing methods.

The open construction makes cleaning very straightforward. Hidden edges and inaccessible corners have been avoided while retaining maximum rigidity. For process validation in the chemical and pharmaceutical industries, certification (GMP) is required. The stainless steel pallet scale fulfils the GMP criteria and is therefore the optimal solution!


The flexible-rod measuring cells are protected against overloading by an overload stop built into the cell.

Self-alignment of the leveling feet by means of rocker pins guarantees optimal according to good manufacturing practice force transmission into the measuring cell

> The handgrip built into the front forks in combination with the wheel set facilitates relocation of the scale.



The open construction makes cleaning very straightforward



Built-in handgrip, self-alignment of the leveling feet, overload stop built into the cell.

Maximum capacity		kg	300	600	1500	3000	
Length of connection cable		m	5				
Protection class	Stainless steel		IP68				
Standard model	Hot-dip galvanized		IP65				
Max. load range (with central loading)		kg	700	1800	3300	3300	
e1/Max1		kg/kg	0.1/300	0.2/600	0.5/1500	1/3000	
Taring range (subtractive)		kg	From 0 to maximum capacity				
Minimum capacity		kg	2	4	10	20	
Zero setting range		kg	+/- 6	+/- 12	+/- 30	+/- 60	
Preload range		kg	-6 +54	-12 +108	-30 +270	-60 +540	
Preload		kg	400	1200	1800	300	
Max. static safe load	Central	kg	700	1800	3300	3300	
	Side	kg	350	900	1900	1900	
	Corner	kg	185	450	950	950	
Weighing accuracy							
Repeatability (s)	1 x 3000e	kg	0.04	0.06	0.15	0.3	
	1 x 6000e SR 2 x 3000e MI						
	3 x 3000e MR	kg	0.02	0.03	0.07	0.15	
Linearity (typical)	1 x 3000e	kg	0.05	0.1	0.2	0.4	
	1 x 6000e SR 2 x 3000e MI 3 x 3000e MR	kg	0.03	0.05	0.1	0.2	

All pallet scales comply with OIML Accuracy Class III and are approved for a temperature range of -10 ... +40 °C.

Accessories



Connection cable extension³

Length 10 m, both ends pluggable, for remote location of the IDNet terminal



Connection set for IDNet terminal*

for stepless lengthening of the connection cable to 100 m, comprising two terminal boxes, box on terminal side with connection cable 2, 5 m long



Special cable on reel*

100 m, in conjunction with the connection set for stepless extension of the IDNet terminal connection

* Only in conjunction with digital terminals



Optional load plate

chrome-nickel steel



Leg widener chrome-nickel steel



Wheel set, chrome-nickel steel

– with plastic rollers

- with chrome-nickel steel rollers for hazardous



chrome-nickel steel




Mounting plate for digital operating terminal, chrome-nickel steel, for mounting the IDNet terminal

on the handle

Mounting plate for analog operating terminal, chrome-nickel steel, for mounting the IND4 terminal

Floor stand

on the handle





Base chrome-nickel steel



COIML

Conformity Quality certificates Worldwide service

Sales and service:



Subject to technical changes © Mettler-Toledo GmbH MCG 11/04 Printed in Germany 22 012 498 www.mt.com

Mettler-Toledo GmbH

CH-8606 Greifensee, Switzerland Tel. +41 1 944 22 11, Fax +41 1 944 30 60 Internet: http://www.mt.com

- AT Mettler-Toledo Ges.m.b.H., A-1230 Wien Tel. (01) 604 1980, Fax (01) 604 2880
- AU Mettler-Toledo Ltd., Port Melbourne, Victoria 3207 Tel. (03) 9644 5700, Fax (03) 9645 3935
- BE n.v. Mettler-Toledo s.a., B-1932 Zaventem el. (02) 334 02 11, Fax (02) 334 03 34
- BR Mettler-Toledo Indústria e Comércio Ltda. São Paulo, CEP 06465-130 Tel. (11) 421 5737, Fax (11) 725 1962
- CA Mettler-Toledo Inc., Toronto, Canada Tel. (905) 612-9777, Fax (905) 612-8561
- CH Mettler-Toledo (Schweiz) AG, CH-8606 Greifensee Tel. 1 944 45 45, Fax 1 944 45 10
- CN Mettler-Toledo (Changzhou) Scale&System Ltd. Changzhou City, Jiangsu 213001 Tel. (519) 664 20 40, Fax (519) 664 19 91
- CZ Mettler-Toledo, s.r.o., CZ-100 00 Praha 10 Tel. (2) 72 123 150, Fax (2) 72 123 170
- DE Mettler-Toledo GmbH, D-35353 Giessen Tel. (0641) 50 70, Fax (0641) 52 951
- DK Mettler-Toledo A/S, DK-2600 Glostrup Tel. (43) 27 08 00, Fax (43) 27 08 28
- ES Mettler-Toledo S.A.E., E-08908 Barcelona Tel. (93) 223 76 00, Fax (93) 223 76 01
- FR Mettler-Toledo s.a., F-78222 Viroflay Tél. (01) 309 717 17, Fax (01) 309 716 16
- HK Mettler-Toledo (HK) Ltd., Kowloon HK,
- Tel. (852) 2744 1221, Fax (852) 2744 6878
- HR Mettler-Toledo, d.o.o., CR-10000 Zagreb Tel. (1) 29 20 633, Fax (1) 29 58 140
- HU Mettler-Toledo Kft, H-1139 Budapest Tel. (1) 288 4040, Fax (1) 288 4050
- IN Mettler-Toledo India Pvt Ltd, Mumbai 400 072 Tel. (022) 2857 0808, Fax (022) 2857 5071
- IT Mettler-Toledo S.p.A., I-20026 Novate Milanese Tel. (02) 333 321, Fax (02) 356 29 73
- JP Mettler-Toledo K.K., Shiromi, J-Osaka 540 Tel. (06) 6949 5901, Fax (06) 6949 5945
- KR Mettler-Toledo (Korea) Ltd., Seoul (137-130) Tel (02) 3498 3500 Fax (02) 3498 3555
- MY Mettler-Toledo (M) Sdn.Bhd., 40150 Selangor Tel. (03) 7845 5773, Fax (03) 7845 8773 MX Mettler-Toledo S.A. de C.V., Mexico CP 06430
- Tel. (5) 547 5700, Fax (5) 541 2228 NL Mettler-Toledo B.V., NL-4000 HA Tiel
- Tel. (0344) 638 363, Fax (0344) 638 390 NO Mettler-Toledo A/S, N-1008 Oslo Tel. (22) 30 44 90, Fax (22) 32 70 02
- PL Mettler-Toledo, Sp. z o.o., PL-02-822 Warszawa Tel. (22) 545 06 80, Fax (22) 545 06 88 RU Mettler-Toledo AG, 10 1000 Moskau
- Tel. (095) 921 68 12, Fax (095) 921 63 53 SE Mettler-Toledo AB, S-12008 Stockholm Tel. (08) 702 50 00, Fax (08) 642 45 62
- SEA Mettler-Toledo (SEA), Reg. Office, 40150 Shah Alam Tel. (03) 7845 5373, Fax (03) 7845 3478
- SG Mettler-Toledo (S) Pte. Ltd., Singapore 139959 Tel. (65) 6890 0011, Fax (65) 6890 0012
- SK Mettler-Toledo, service s.r.o., SK-83103 Bratislava Tel. (7) 525 2170, Fax (7) 525 2173
- SI Mettler-Toledo, d.o.o., SI-1236 Trzin Tel. (1) 562 1801, Fax (1) 562 1789 TH Mettler-Toledo (Thailand), Bangkok 10310
- Tel. (02) 723 0300, Fax (02) 719 6479 TW Mettler-Toledo Pac Rim AG, Taipei Tel. (02) 2657 8898, Fax (02) 26557 0776
- UK Mettler-Toledo Ltd., Leicester, LE4 1AW Tel. (0116) 235 0888, Fax (0116) 236 5500
- US Mettler-Toledo, Inc., Columbus, Ohio 43240 Tel. (614) 438 4511, Fax (614) 438 4900

For all other countries: Mettler-Toledo GmbH PO Box VI-400, CH-8606 Greifensee Tel. +41 1 944 22 11, Fax +41 1 944 31 70

PTA455 / PTA459 pallet scale

For maximum flexibility when weighing pallets:

- in goods receiving/shipping
- in manufacturing
- in packaging



- Several resolutions
- Tailored solutions
- Numerous options & comprehensive accessories

A pallet scale for every situation

