

BBA242 Refinish Scales

For Today's Automotive Body Shop



Full graphic display

The backlit LCD display with graphic capability allows full text and multi language communication and guides you through your paint mixes with ease.



Safe to use

The BBA242 meets all pertinent international hazardous area standards to ensure your safety.



True industrial design

The BBA242 has been developed for the ruggedness of the automotive body shop environment.



Fast and easy to use

The BBA242form can store up to 20 formulas locally, which you can download from a PC with paint mixing software. During the mixes you work locally on the scale and do not block the PC.



Zone 1, Division 1



BBA242



The BBA242form paint scale brings a new level of comfort and functionality into the automotive body shop. An easy interface allows you to download up to 20 recipes from a PC. The graphic display of the BBA242form guides you through the mixing process and stores the mixing protocol inside the scale. Automated correction modes can be accessed in case you add too much of a component. The BBA242paint offers all the features of the BBA242form except the formula mode, making it a perfect solution for PC based mixing control.

METTLER TOLEDO

Operation and maintenance

The BBA242 paint scales can easily be connected to a PC, where you run your paint mixing software. If you work in a hazardous area environment, various approved version of the BBA242 are available. The PC itself must be installed in a safe area and connects via different available interfaces. In case you pour paint over the weighing base, it can easily be cleaned thanks to the stainless steel platform.

Dimensions of the BBA242 Scale (mm)



Technical Data

BBA242 Refinish Paint Scales

Capacity	0 – 7.1kg
Readability	0.1g (0.05g up to 999g)
Display	Backlit graphic LCD, 192*64 pixel
Languages	English, German, Italian, French, Spanish, Chinese
Formula memory (BBA242form)	Up to 20 formulas with 15 components
Keypad	7 function keys
Housing	Cast aluminum
Platform	Stainless steel
Protection	IP54
Interfaces	RS232, USB, connectable to various color mixing systems
Power	120/230 VAC power supplies for hazardous areas, universal power supply for safe areas
Ambient temperature range	0°C to +40°C
Hazardous area approvals	BBA242x: ATEX: II 2 G Ex ib IIB T4 IECEX: Ex ib IIB T4 FM: IS Class I Div 1, Groups C & D T4 CSA: IS Class I, Div 1 Group C & D T4 BBA242xx: ATEX: II 3 G Ex nL IIB T4 IECEX: Ex nL IIB T4

Models

BBA242paint
BBA242paint USB
BBA242 OIML
BBA242x paint
BBA242x paint USB
BBA242x form
BBA242x form USB
BBA242xx paint
BBA242xx form

Accessories

APS242x USB

Panda-EX1P
72262434
71153871

Description

For use in safe areas
For use in safe areas, USB converter
Legal for trade applications
For use in zone 1 and Cl I, Div 1
For use in zone 1 and Cl I, Div 1
For use in zone 1 and Cl I, Div 1
For use in zone 1 and Cl I, Div 1
For use in zone 2
For use in zone 2

Intrinsically safe power supply with integrated barrier for USB interface, 25 m cable
Intrinsically safe power supply, 10m cable
Protection cover weighing pan
Protection cover scale head



Mettler-Toledo AG

CH-8606 Greifensee
Switzerland
Tel. +41 44 944 22 11
Fax +41 44 944 30 60

Subject to technical changes
© 01/2013 Mettler-Toledo AG

www.mt.com

For more information